

## COMPETITIVE ADVANTAGE ANALYSIS



### STERAMIST<sup>®</sup> iHP<sup>™</sup>

VS.

### MANUAL CLEANING METHODS

- |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• Features a particle size as low as 0.05 microns to reach spaces most traditional cleaners cannot</li> <li>• Gentle, non-corrosive application</li> <li>• Kills on contact with 5-second application time per square foot</li> <li>• Handheld applicator assists in distributing solution evenly over surfaces</li> <li>• BIT solution is ready-to-go and requires no dilution</li> <li>• SteraMist Environment System features multi-applicator functionality for simultaneous room disinfection</li> <li>• No wiping and no rinsing required</li> <li>• Leaves no residue behind after treatment</li> <li>• Handheld application and remote start functionality allows for no-touch disinfection</li> <li>• Solution propellant allows for the disinfection of high, hard-to-reach areas</li> </ul> | <ul style="list-style-type: none"> <li>• Relies on surface coverage with cleaner, leading to many untreated areas</li> <li>• Relies on physical contact of cleaning medium to surface, risking abrasion and wear-and-tear</li> <li>• Depending on the method of application, may require longer application times</li> <li>• Physical application risks uneven application and oversight</li> <li>• Many cleaning agents require dilution and mixture before application</li> <li>• Physical labor often limits application capability and restricts the cleaner to a single area at a time</li> <li>• Physical cleaning requires contact through wiping or rinsing</li> <li>• May leave behind residual bacterial or streaks</li> <li>• Requires direct interaction with contaminated surfaces</li> <li>• Limits vertical reach and restricts access to awkward or tight areas</li> </ul> |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

QUICK. EASY. EFFECTIVE.  
DISINFECT WITH **STERAMIST**<sup>®</sup> TODAY.

For Service Call Regency DRT  
888.221.5791